



**FAG****X-life****7006-B-XL-2RS-TVP-UO**

Angular contact ball bearing

Angular contact ball bearing 70..-B-XL-2RS-TVP, single row, X-life, seals, plastic cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	2RS	Contact seal on both sides
Cage	TVP	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Bearing with matched conditions for fitting in pairs	UO	Bearing set clearance-free in O or X arrangement
Lubricant	GA14	Ball bearing grease, low noise

Main Dimensions & Performance Data

d	30 mm	Bore diameter
D	55 mm	Outside diameter
B	13 mm	Width
C _r	19.900 N	Basic dynamic load rating, radial
C _{0r}	13.400 N	Basic static load rating, radial
C _{ur}	930 N	Fatigue load limit, radial
n _G	6.900 1/min	Limiting speed
≈m	0,113 kg	Weight



Mounting dimensions

$d_{a \min}$	34,6 mm	Minimum diameter of shaft shoulder
$D_{a \max}$	50,4 mm	Maximum diameter of housing shoulder
$D_{b \max}$	51,8 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1 mm	Maximum fillet radius of shaft
$r_{a1 \max}$	0,6 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
$r_{1 \min}$	0,6 mm	Minimum chamfer dimension
D_1	47,05 mm	Shoulder diameter on outer ring wide side face
D_2	47,7 mm	Caliber diameter on outer ring wide side face
D_3	51,93 mm	Caliber diameter on outer ring small side face
d_1	41,26 mm	Shoulder diameter on inner ring wide side face
d_2	38,04 mm	Caliber diameter on inner ring wide side face
a	24,9 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Additional information

$Tol (+)$	8 μm	Tolerance for axial clearance or preload per set
$A_{\min}$	0 mm	Axial clearance per set min.



Characteristics

-  Radial load
-  Axial load in one direction
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides