



**FAG****X-life****7206-B-XL-2RS-TVP-UL**

Angular contact ball bearing

Angular contact ball bearing 72...-B-XL-2RS-TVP, single row, X-life, seals, plastic cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	2RS	Contact seal on both sides
Cage	TVP	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Bearing with matched conditions for fitting in pairs	UL	Bearing set with light preload
Lubricant	GA14	Ball bearing grease, low noise

Main Dimensions & Performance Data

d	30 mm	Bore diameter
D	62 mm	Outside diameter
B	16 mm	Width
C _r	23.100 N	Basic dynamic load rating, radial
C _{0r}	14.100 N	Basic static load rating, radial
C _{ur}	980 N	Fatigue load limit, radial
n _G	6.500 1/min	Limiting speed
≈m	0,208 kg	Weight



Mounting dimensions

$d_{a \min}$	35,6 mm	Minimum diameter of shaft shoulder
$D_{a \max}$	56,4 mm	Maximum diameter of housing shoulder
$D_{b \max}$	57,8 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1 mm	Maximum fillet radius of shaft
$r_{a1 \max}$	0,6 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
$r_1 \min$	0,6 mm	Minimum chamfer dimension
D_1	49,52 mm	Shoulder diameter on outer ring wide side face
D_2	51,65 mm	Caliber diameter on outer ring wide side face
D_3	57,07 mm	Caliber diameter on outer ring small side face
d_1	43,2 mm	Shoulder diameter on inner ring wide side face
d_2	39,49 mm	Caliber diameter on inner ring wide side face
a	27,3 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Additional information

$V_{\max}$	-6 μm	Preload per set max.
Tol (+)	8 μm	Tolerance for axial clearance or preload per set
$F_{V \max}$	157 N	Preload force



Characteristics

-  Radial load
-  Axial load in one direction
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides