



**FAG****X-life****7202-B-XL-2RS-TVP-UO**

Angular contact ball bearing

Angular contact ball bearing 72...-B-XL-2RS-TVP, single row, X-life, seals, plastic cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	2RS	Contact seal on both sides
Cage	TVP	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Bearing with matched conditions for fitting in pairs	UO	Bearing set clearance-free in O or X arrangement
Lubricant	GA14	Ball bearing grease, low noise

Main Dimensions & Performance Data

d	15 mm	Bore diameter
D	35 mm	Outside diameter
B	11 mm	Width
C _r	8.900 N	Basic dynamic load rating, radial
C _{0r}	4.450 N	Basic static load rating, radial
C _{ur}	305 N	Fatigue load limit, radial
n _G	12.800 1/min	Limiting speed
≈m	0,046 kg	Weight



Mounting dimensions

$d_{a \min}$	19,2 mm	Minimum diameter of shaft shoulder
$D_{a \max}$	30,8 mm	Maximum diameter of housing shoulder
$D_{b \max}$	32,6 mm	Maximum diameter of housing shoulder
$r_{a \max}$	0,6 mm	Maximum fillet radius of shaft
$r_{a1 \max}$	0,3 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
$r_{1 \min}$	0,3 mm	Minimum chamfer dimension
D_1	27,63 mm	Shoulder diameter on outer ring wide side face
D_2	29,19 mm	Caliber diameter on outer ring wide side face
D_3	32,1 mm	Caliber diameter on outer ring small side face
d_1	22,76 mm	Shoulder diameter on inner ring wide side face
d_2	19,7 mm	Caliber diameter on inner ring wide side face
a	16 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Additional information

$Tol (+)$	8 μm	Tolerance for axial clearance or preload per set
$A_{\min}$	0 mm	Axial clearance per set min.



View product details on medias

01.09.2026, 21:58:56 UTC

SCHAEFFLER

Characteristics



Radial load



Axial load in one direction



Lifetime lubrication, freedom from maintenance



Grease Lubrication



Sealed on both sides