



**FAG****X-life****7211-B-XL-MP** [↗](#)

Angular contact ball bearing

Angular contact ball bearing 72..-B-XL-MP,
single row, X-life, solid brass cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	Without	Not sealed
Cage	MP	Solid brass cage, ball guided
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	55 mm	Bore diameter
D	100 mm	Outside diameter
B	21 mm	Width
C _r	52.000 N	Basic dynamic load rating, radial
C _{0r}	38.500 N	Basic static load rating, radial
C _{ur}	2.650 N	Fatigue load limit, radial
n _G	11.900 1/min	Limiting speed
n _{gr}	6.800 1/min	Reference speed
m	0,68 kg	Weight



Mounting dimensions

$d_{a \min}$	64 mm	Minimum diameter of shaft shoulder
$D_{a \max}$	91 mm	Maximum diameter of housing shoulder
$D_{b \max}$	94,4 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1,5 mm	Maximum fillet radius of shaft
$r_{a1 \max}$	1 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	1,5 mm	Minimum chamfer dimension
$r_1 \min$	1 mm	Minimum chamfer dimension
D_1	83 mm	Shoulder diameter on outer ring wide side face
d_1	72,56 mm	Shoulder diameter on inner ring wide side face
a	43 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed