



FAG




7219-B-XL-MP-UA

Angular contact ball bearing

Angular contact ball bearing 72..-B-XL-MP,
single row, X-life, solid brass cage

X-life

Technical information



Your current product variant

Design variant	B	B
Type of Seal	Without	Not sealed
Cage	MP	Solid brass cage, ball guided
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Bearing with matched conditions for fitting in pairs	UA	Bearing set with small axial internal clearance
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	95 mm	Bore diameter
D	170 mm	Outside diameter
B	32 mm	Width
C _r	123.000 N	Basic dynamic load rating, radial
C _{0r}	106.000 N	Basic static load rating, radial
C _{ur}	6.400 N	Fatigue load limit, radial
n _G	6.700 1/min	Limiting speed
n _{gr}	4.450 1/min	Reference speed
m	2,98 kg	Weight



Mounting dimensions

$d_{a\ min}$	107 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	158 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	163 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2,1 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	1 mm	Maximum fillet radius of housing

Dimensions

$r_{\ min}$	2,1 mm	Minimum chamfer dimension
$r_{1\ min}$	1,1 mm	Minimum chamfer dimension
D_1	141,5 mm	Shoulder diameter on outer ring wide side face
d_1	125,3 mm	Shoulder diameter on inner ring wide side face
a	71,6 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	150 °C	Operating temperature max.

Additional information

Tol (+)	12 µm	Tolerance for axial clearance or preload per set
$A_{\ min}$	54 mm	Axial clearance per set min.

Characteristics

	Radial load
	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed