



**FAG****X-life****7210-B-XL-TVP-UA**

Angular contact ball bearing

Angular contact ball bearing 72...-B-XL-TVP,
single row, X-life, plastic cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	Without	Not sealed
Cage	TVP	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Bearing with matched conditions for fitting in pairs	UA	Bearing set with small axial internal clearance
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	90 mm	Outside diameter
B	20 mm	Width
C _r	41.500 N	Basic dynamic load rating, radial
C _{0r}	28.500 N	Basic static load rating, radial
C _{ur}	1.970 N	Fatigue load limit, radial
n _G	10.300 1/min	Limiting speed
n _{gr}	7.600 1/min	Reference speed
≈m	0,47 kg	Weight



Mounting dimensions

$d_{a\ min}$	57 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	83 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	85,8 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	1 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	0,6 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
$r_{1\ min}$	0,6 mm	Minimum chamfer dimension
D_1	74,78 mm	Shoulder diameter on outer ring wide side face
d_1	66,26 mm	Shoulder diameter on inner ring wide side face
a	39,4 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Additional information

Tol (+)	8 µm	Tolerance for axial clearance or preload per set
$A_{\min}$	44 mm	Axial clearance per set min.

Characteristics

	Radial load
	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed