



**FAG****X-life****7308-B-XL-2RS-TVP**

Angular contact ball bearing

Angular contact ball bearing 73...-B-XL-2RS-TVP, single row, X-life, seals, plastic cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	2RS	Contact seal on both sides
Cage	TVP	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	GA13	Ball bearing and insert bearing grease

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	90 mm	Outside diameter
B	23 mm	Width
C _r	57.000 N	Basic dynamic load rating, radial
C _{0r}	34.500 N	Basic static load rating, radial
C _{ur}	2.390 N	Fatigue load limit, radial
n _G	4.650 1/min	Limiting speed
≈m	0,631 kg	Weight



Mounting dimensions

$d_{a\ min}$	49 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	81 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	84,4 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	1,5 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	1 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	1,5 mm	Minimum chamfer dimension
$r_{1\ min}$	1 mm	Minimum chamfer dimension
D_1	71,28 mm	Shoulder diameter on outer ring wide side face
D_2	73,88 mm	Caliber diameter on outer ring wide side face
D_3	83,34 mm	Caliber diameter on outer ring small side face
d_1	59,99 mm	Shoulder diameter on inner ring wide side face
d_2	55,58 mm	Caliber diameter on inner ring wide side face
a	38,8 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides