



**FAG****X-life****7318-B-XL-MP-UA**

Angular contact ball bearing

Angular contact ball bearing 73..-B-XL-MP,
single row, X-life, solid brass cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	Without	Not sealed
Cage	MP	Solid brass cage, ball guided
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Bearing with matched conditions for fitting in pairs	UA	Bearing set with small axial internal clearance
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	90 mm	Bore diameter
D	190 mm	Outside diameter
B	43 mm	Width
C _r	171.000 N	Basic dynamic load rating, radial
C _{0r}	144.000 N	Basic static load rating, radial
C _{ur}	8.400 N	Fatigue load limit, radial
n _G	6.100 1/min	Limiting speed
n _{gr}	3.950 1/min	Reference speed
m	5,59 kg	Weight



Mounting dimensions

$d_{a\ min}$	104 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	176 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	183 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2,5 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	1 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
$r_{1\ min}$	1,1 mm	Minimum chamfer dimension
D_1	152,14 mm	Shoulder diameter on outer ring wide side face
d_1	130,3 mm	Shoulder diameter on inner ring wide side face
a	80,2 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.

Additional information

Tol (+)	12 µm	Tolerance for axial clearance or preload per set
$A_{\min}$	54 mm	Axial clearance per set min.

Characteristics

	Radial load
	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed