

**FAG****X-life****7316-B-XL-TVP-UA**

Angular contact ball bearing

Angular contact ball bearing 73...-B-XL-TVP,
single row, X-life, plastic cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	Without	Not sealed
Cage	TVP	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Bearing with matched conditions for fitting in pairs	UA	Bearing set with small axial internal clearance
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	80 mm	Bore diameter
D	170 mm	Outside diameter
B	39 mm	Width
C _r	155.000 N	Basic dynamic load rating, radial
C _{0r}	124.000 N	Basic static load rating, radial
C _{ur}	7.700 N	Fatigue load limit, radial
n _G	5.200 1/min	Limiting speed
n _{gr}	4.250 1/min	Reference speed
≈m	3,65 kg	Weight



Mounting dimensions

$d_{a\ min}$	92 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	158 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	163 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2,1 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	1 mm	Maximum fillet radius of housing

Dimensions

$r_{\ min}$	2,1 mm	Minimum chamfer dimension
$r_{1\ min}$	1,1 mm	Minimum chamfer dimension
D_1	136,7 mm	Shoulder diameter on outer ring wide side face
d_1	115,7 mm	Shoulder diameter on inner ring wide side face
a	71,9 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	120 °C	Operating temperature max.

Additional information

Tol (+)	12 µm	Tolerance for axial clearance or preload per set
$A_{\ min}$	50 mm	Axial clearance per set min.

Characteristics

	Radial load
	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed