



**FAG****X-life****7408-B-XL-MP-UA**

Angular contact ball bearing

Angular contact ball bearing 74..-B-XL-MP,
single row, X-life, solid brass cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	Without	Not sealed
Cage	MP	Solid brass cage, ball guided
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Bearing with matched conditions for fitting in pairs	UA	Bearing set with small axial internal clearance
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	110 mm	Outside diameter
B	27 mm	Width
C _r	75.000 N	Basic dynamic load rating, radial
C _{0r}	50.000 N	Basic static load rating, radial
C _{ur}	3.500 N	Fatigue load limit, radial
n _G	10.900 1/min	Limiting speed
n _{gr}	5.000 1/min	Reference speed
m	1,425 kg	Weight



Mounting dimensions

$d_{a\ min}$	53 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	97 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	104,4 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	1 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	2 mm	Minimum chamfer dimension
$r_{1\ min}$	1 mm	Minimum chamfer dimension
D_1	87,6 mm	Shoulder diameter on outer ring wide side face
d_1	73,1 mm	Shoulder diameter on inner ring wide side face
a	47,1 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.

Additional information

$Tol\ (+)$	12 μm	Tolerance for axial clearance or preload per set
$A_{\min}$	40 mm	Axial clearance per set min.

Characteristics

	Radial load
	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed