



**3008-2RS**

Angular contact ball bearing

Angular contact ball bearing 30...-B-2RS-TVH,
double row, seals, plastic cage

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Sealing	2RS	Contact seal on both sides
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	GA13	Ball bearing and insert bearing grease
Axial internal clearance	CN	Group N (CN)

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	68 mm	Outside diameter
B	21 mm	Width
C _r	25.000 N	Basic dynamic load rating, radial
C _{0r}	21.300 N	Basic static load rating, radial
C _{ur}	1.110 N	Fatigue load limit, radial
n _G	5.600 1/min	Limiting speed
m	0,25 kg	Weight



Mounting dimensions

$d_{a \min}$	44,6 mm	Minimum diameter shaft shoulder
$D_{a \max}$	63,4 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
D_1	59,04 mm	Shoulder diameter outer ring
D_2	61,22 mm	Caliber diameter outer ring
d_1	49,2 mm	Shoulder diameter inner ring
d_2	46,85 mm	Caliber diameter inner ring
a	33,4 mm	Distance between the apexes of the pressure cones
α	25 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides