



**3006-2Z**

Angular contact ball bearing

Angular contact ball bearing 30..-B-2Z-TVH,
double row, shields, plastic cage

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Sealing	2Z	Non-contact shield on both sides
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	GA13	Ball bearing and insert bearing grease
Axial internal clearance	CN	Group N (CN)

Main Dimensions & Performance Data

d	30 mm	Bore diameter
D	55 mm	Outside diameter
B	19 mm	Width
C _r	19.900 N	Basic dynamic load rating, radial
C _{0r}	15.400 N	Basic static load rating, radial
C _{ur}	800 N	Fatigue load limit, radial
n _G	10.100 1/min	Limiting speed
n _{gr}	10.100 1/min	Reference speed
≈m	0,168 kg	Weight



Mounting dimensions

$d_{a\ min}$	34,6 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	50,4 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
D_1	46,92 mm	Shoulder diameter outer ring
D_2	49,05 mm	Caliber diameter outer ring
d_1	37,7 mm	Shoulder diameter inner ring
d_2	35,68 mm	Caliber diameter inner ring
a	27,4 mm	Distance between the apexes of the pressure cones
α	25 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides