






FAG

B7014-C-2RSD-T-P4S-UL

Spindle bearing

Spindle bearing B70...-C-2RSD, adjusted, in pairs or sets, contact angle $\alpha = 15^\circ$, lip seals on both sides, non-contact, restricted tolerances

Technical information



Your current product variant

Preload	L	Preload light
Contact angle	C	Contact angle 15°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing
Lubricant	GA21	Grease for super precision bearings, standard

Main Dimensions & Performance Data

d	70 mm	Bore diameter
D	110 mm	Outside diameter
B	20 mm	Width
C _r	50.000 N	Basic dynamic load rating, radial
C _{0r}	30.500 N	Basic static load rating, radial
C _{ur}	3.250 N	Fatigue load limit, radial
n _{G Grease}	13.000 1/min	Limiting speed for grease lubrication
≈m	0,59 kg	Weight



Mounting dimensions

d_a	77 mm	Diameter shaft shoulder
d_a	H12	Diameter shaft shoulder clearance
D_a	102 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	0,6 mm	Maximum recess radius
a	22,1 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
$r_{1 \min}$	1,1 mm	Minimum chamfer dimension
α	15 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	80 °C	Operating temperature max.

Additional information

F_{VL}	276 N	Preload force light
F_{VM}	894 N	Preload force medium
F_{VH}	1.790 N	Preload force heavy
K_{aEL}	853 N	Lift-off force light
K_{aEM}	2.995 N	Lift-off force medium
K_{aEH}	6.414 N	Lift-off force heavy
c_{aL}	74 N/μm	Axial rigidity light
c_{aM}	125 N/μm	Axial rigidity medium
c_{aH}	179 N/μm	Axial rigidity heavy



Characteristics

-  Radial load
-  Axial load in one direction
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides