



FAG



3202-BD-XL-TVH

Angular contact ball bearing

Angular contact ball bearing 32...BD-XL-TVH, double row, X-life, plastic cage

X-life

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Changed internal design	D	D
Type of Seal	Without	Not sealed
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Axial internal clearance	CN	Group N (CN)

Main Dimensions & Performance Data

d	15 mm	Bore diameter
D	35 mm	Outside diameter
B	15,9 mm	Width
C _r	12.600 N	Basic dynamic load rating, radial
C _{0r}	7.400 N	Basic static load rating, radial
C _{ur}	520 N	Fatigue load limit, radial
n _G	22.300 1/min	Limiting speed
n _{gr}	18.500 1/min	Reference speed
m	0,062 kg	Weight



Mounting dimensions

$d_{a\ min}$	19,2 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	30,8 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	0,6 mm	Maximum fillet radius

Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
D_1	29,35 mm	Shoulder diameter outer ring
D_2	31,13 mm	Caliber diameter outer ring
d_1	22,2 mm	Shoulder diameter inner ring
d_2	20,96 mm	Caliber diameter inner ring
a	20,7 mm	Distance between the apexes of the pressure cones
α	30 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed