



**FAG****X-life****3303-BD-XL-TVH**

Angular contact ball bearing

Angular contact ball bearing 33...BD-XL-TVH,
double row, X-life, plastic cage

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Changed internal design	D	D
Type of Seal	Without	Not sealed
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Axial internal clearance	CN	Group N (CN)

Main Dimensions & Performance Data

d	17 mm	Bore diameter
D	47 mm	Outside diameter
B	22,2 mm	Width
C _r	22.500 N	Basic dynamic load rating, radial
C _{0r}	13.100 N	Basic static load rating, radial
C _{ur}	910 N	Fatigue load limit, radial
n _G	16.600 1/min	Limiting speed
n _{gr}	12.600 1/min	Reference speed
m	0,171 kg	Weight



Mounting dimensions

$d_{a \min}$	22,6 mm	Minimum diameter shaft shoulder
$D_{a \max}$	41,4 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
D_1	38,97 mm	Shoulder diameter outer ring
D_2	41,13 mm	Caliber diameter outer ring
d_1	28,52 mm	Shoulder diameter inner ring
d_2	27,14 mm	Caliber diameter inner ring
a	27,5 mm	Distance between the apexes of the pressure cones
α	30 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed