

**FAG****B7028-C-T-P4S-UL**

Spindle bearing

Spindle bearing B70...-C, adjusted, in pairs or sets, contact angle $\alpha = 15^\circ$, restricted tolerances

Technical information




Your current product variant

Preload	L	Preload light
Contact angle	C	Contact angle 15°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	Without	Not sealed
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing

Main Dimensions & Performance Data

d	140 mm	Bore diameter
D	210 mm	Outside diameter
B	33 mm	Width
C_r	153.000 N	Basic dynamic load rating, radial
C_{0r}	114.000 N	Basic static load rating, radial
C_{ur}	9.100 N	Fatigue load limit, radial
$n_{G \text{ Grease}}$	6.300 1/min	Limiting speed for grease lubrication
$n_{G \text{ Oil}}$	10.000 1/min	Limiting speed for oil lubrication
$\approx m$	3,288 kg	Weight





Mounting dimensions

d _a	152 mm	Diameter shaft shoulder
d _a	h12	Diameter shaft shoulder clearance
D _a	199 mm	Shoulder diameter outer ring
D _a	H12	Shoulder diameter outer ring clearance
r _a max	2 mm	Maximum recess radius
r _{a1} max	1 mm	Maximum recess radius
E _{tk} min	161,6 mm	Minimum diameter injection pitch
E _{tk} max	169,2 mm	Maximum diameter injection pitch
E _{tk1} min	161,6 mm	Minimum diameter injection pitch
E _{tk1} max	169,2 mm	Maximum diameter injection pitch
a	39,9 mm	Distance between the apexes of the pressure cones

Dimensions

r _{min}	2 mm	Minimum chamfer dimension
r ₁ min	2 mm	Minimum chamfer dimension
α	15 °	Contact angle

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	100 °C	Operating temperature max.



Additional information

F_{VL}	866 N	Preload force light
F_{VM}	2.724 N	Preload force medium
F_{VH}	5.429 N	Preload force heavy
K_{aEL}	2.661 N	Lift-off force light
K_{aEM}	9.007 N	Lift-off force medium
K_{aEH}	19.129 N	Lift-off force heavy
c_{aL}	142 N/μm	Axial rigidity light
c_{aM}	237 N/μm	Axial rigidity medium
c_{aH}	335 N/μm	Axial rigidity heavy

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed