


**FAG****B7013-E-2RSD-T-P4S-UL**

Spindle bearing

Spindle bearing B70...-E-2RSD, adjusted, in pairs or sets, contact angle $\alpha = 25^\circ$, lip seals on both sides, non-contact, restricted tolerances

Technical information



Your current product variant

Preload	L	Preload light
Contact angle	E	Contact angle 25°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	2RSD	Non-contact sealed on both sides and greased "for life"
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing
Lubricant	GA21	Grease for super precision bearings, standard

Main Dimensions & Performance Data

d	65 mm	Bore diameter
D	100 mm	Outside diameter
B	18 mm	Width
C _r	39.000 N	Basic dynamic load rating, radial
C _{0r}	24.100 N	Basic static load rating, radial
C _{ur}	2.550 N	Fatigue load limit, radial
n _G Grease	13.000 1/min	Limiting speed for grease lubrication
≈m	420,99 g	Weight



Mounting dimensions

d_a	72 mm	Diameter shaft shoulder
d_a	H12	Diameter shaft shoulder clearance
D_a	93 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	0,6 mm	Maximum recess radius
a	28,2 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
$r_{1 \min}$	1,1 mm	Minimum chamfer dimension
α	25 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	80 °C	Operating temperature max.

Additional information

F_{VL}	308 N	Preload force light
F_{VM}	1.111 N	Preload force medium
F_{VH}	2.350 N	Preload force heavy
K_{aEL}	896 N	Lift-off force light
K_{aEM}	3.347 N	Lift-off force medium
K_{aEH}	7.323 N	Lift-off force heavy
c_{aL}	154 N/μm	Axial rigidity light
c_{aM}	251 N/μm	Axial rigidity medium
c_{aH}	342 N/μm	Axial rigidity heavy



Characteristics



Radial load



Axial load in one direction



Lifetime lubrication, freedom from maintenance



Grease Lubrication



Sealed on both sides