


**FAG****B7018-C-2RSD-T-P4S-UL**

Spindle bearing

Spindle bearing B70...-C-2RSD, adjusted, in pairs or sets, contact angle $\alpha = 15^\circ$, lip seals on both sides, non-contact, restricted tolerances

Technical information



Your current product variant

Preload	L	Preload light
Contact angle	C	Contact angle 15°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	2RSD	Non-contact sealed on both sides and greased "for life"
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing
Lubricant	GA21	Grease for super precision bearings, standard

Main Dimensions & Performance Data

d	90 mm	Bore diameter
D	140 mm	Outside diameter
B	24 mm	Width
C_r	78.000 N	Basic dynamic load rating, radial
C_{0r}	51.000 N	Basic static load rating, radial
C_{ur}	5.000 N	Fatigue load limit, radial
n_G Grease	10.000 1/min	Limiting speed for grease lubrication
$\approx m$	1,15 kg	Weight



Mounting dimensions

d_a	100 mm	Diameter shaft shoulder
d_a	H12	Diameter shaft shoulder clearance
D_a	131 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1,5 mm	Maximum recess radius
$r_{a1 \max}$	0,6 mm	Maximum recess radius
a	27,4 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	1,5 mm	Minimum chamfer dimension
$r_{1 \min}$	1,5 mm	Minimum chamfer dimension
α	15 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	80 °C	Operating temperature max.

Additional information

F_{VL}	437 N	Preload force light
F_{VM}	1.395 N	Preload force medium
F_{VH}	2.785 N	Preload force heavy
K_{aEL}	1.347 N	Lift-off force light
K_{aEM}	4.651 N	Lift-off force medium
K_{aEH}	9.920 N	Lift-off force heavy
c_{aL}	95 N/μm	Axial rigidity light
c_{aM}	161 N/μm	Axial rigidity medium
c_{aH}	229 N/μm	Axial rigidity heavy



Characteristics

-  Radial load
-  Axial load in one direction
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides