


**FAG****B71911-C-2RSD-T-P4S-UL**

Spindle bearing

Spindle bearing B719...-C-2RSD, adjusted, in pairs or sets, contact angle $\alpha = 15^\circ$, lip seals on both sides, non-contact, restricted tolerances

Technical information



Your current product variant

Preload	L	Preload light
Contact angle	C	Contact angle 15°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	2RSD	Non-contact sealed on both sides and greased "for life"
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing
Lubricant	GA21	Grease for super precision bearings, standard

Main Dimensions & Performance Data

d	55 mm	Bore diameter
D	80 mm	Outside diameter
B	13 mm	Width
C_r	23.500 N	Basic dynamic load rating, radial
C_{0r}	14.400 N	Basic static load rating, radial
C_{ur}	1.530 N	Fatigue load limit, radial
n_G Grease	17.000 1/min	Limiting speed for grease lubrication
$\approx m$	172,88 g	Weight



Mounting dimensions

d_a	60 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	75,5 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	0,6 mm	Maximum recess radius
$r_{a1 \max}$	0,3 mm	Maximum recess radius
a	15,5 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
$r_1 \min$	1 mm	Minimum chamfer dimension
α	15 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	80 °C	Operating temperature max.

Additional information

F_{VL}	111 N	Preload force light
F_{VM}	382 N	Preload force medium
F_{VH}	780 N	Preload force heavy
K_{aEL}	340 N	Lift-off force light
K_{aEM}	1.274 N	Lift-off force medium
K_{aEH}	2.784 N	Lift-off force heavy
c_{aL}	51 N/μm	Axial rigidity light
c_{aM}	89 N/μm	Axial rigidity medium
c_{aH}	128 N/μm	Axial rigidity heavy



Characteristics

-  Radial load
-  Axial load in one direction
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides