
**FAG****B7011-C-T-P4S-UL** **Spindle bearing**

Spindle bearing B70...-C, adjusted, in pairs or sets, contact angle $\alpha = 15^\circ$, restricted tolerances



Technical information

**Your current product variant**

Preload	L	Preload light
Contact angle	C	Contact angle 15°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	Without	Not sealed
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing

Main Dimensions & Performance Data

d	55 mm	Bore diameter
D	90 mm	Outside diameter
B	18 mm	Width
C_r	38.500 N	Basic dynamic load rating, radial
C_{0r}	22.100 N	Basic static load rating, radial
C_{ur}	2.340 N	Fatigue load limit, radial
n_G Grease	16.000 1/min	Limiting speed for grease lubrication
$n_{G\text{ Oil}}$	24.000 1/min	Limiting speed for oil lubrication
$\approx m$	371,02 g	Weight





Mounting dimensions

d_a	62 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	83 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	0,6 mm	Maximum recess radius
$E_{tk \min}$	65,9 mm	Minimum diameter injection pitch
$E_{tk \max}$	69,6 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	65,9 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	69,6 mm	Maximum diameter injection pitch
a	18,7 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
$r_{1 \min}$	1,1 mm	Minimum chamfer dimension
α	15 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.



Additional information

F_{VL}	205 N	Preload force light
F_{VM}	670 N	Preload force medium
F_{VH}	1.344 N	Preload force heavy
K_{aEL}	635 N	Lift-off force light
K_{aEM}	2.253 N	Lift-off force medium
K_{aEH}	4.837 N	Lift-off force heavy
c_{aL}	61 N/μm	Axial rigidity light
c_{aM}	106 N/μm	Axial rigidity medium
c_{aH}	151 N/μm	Axial rigidity heavy

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed