


**FAG****B7006-E-2RSD-T-P4S-UL**

Spindle bearing

Spindle bearing B70...-E-2RSD, adjusted, in pairs or sets, contact angle $\alpha = 25^\circ$, lip seals on both sides, non-contact, restricted tolerances

Technical information



Your current product variant

Preload	L	Preload light
Contact angle	E	Contact angle 25°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	2RSD	Non-contact sealed on both sides and greased "for life"
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing
Lubricant	GA21	Grease for super precision bearings, standard

Main Dimensions & Performance Data

d	30 mm	Bore diameter
D	55 mm	Outside diameter
B	13 mm	Width
C_r	13.700 N	Basic dynamic load rating, radial
C_{0r}	6.400 N	Basic static load rating, radial
C_{ur}	670 N	Fatigue load limit, radial
n_G Grease	24.000 1/min	Limiting speed for grease lubrication
$\approx m$	109,17 g	Weight



Mounting dimensions

d_a	36 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	49 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	0,3 mm	Maximum recess radius
a	16,5 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
$r_{1 \min}$	1 mm	Minimum chamfer dimension
α	25 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	80 °C	Operating temperature max.

Additional information

F_{VL}	102 N	Preload force light
F_{VM}	396 N	Preload force medium
F_{VH}	854 N	Preload force heavy
K_{aEL}	294 N	Lift-off force light
K_{aEM}	1.188 N	Lift-off force medium
K_{aEH}	2.661 N	Lift-off force heavy
c_{aL}	74 N/μm	Axial rigidity light
c_{aM}	123 N/μm	Axial rigidity medium
c_{aH}	170 N/μm	Axial rigidity heavy



Characteristics

-  Radial load
-  Axial load in one direction
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides