

**FAG****B7014-E-T-P4S-UL** **Spindle bearing**


Spindle bearing B70..-E, adjusted, in pairs or sets, contact angle $\alpha = 25^\circ$, restricted tolerances

Technical information**Your current product variant**

Preload	L	Preload light
Contact angle	E	Contact angle 25°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Type of Seal	Without	Not sealed
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing

Main Dimensions & Performance Data

d	70 mm	Bore diameter
D	110 mm	Outside diameter
B	20 mm	Width
C_r	48.000 N	Basic dynamic load rating, radial
C_{0r}	29.000 N	Basic static load rating, radial
C_{ur}	3.100 N	Fatigue load limit, radial
n_G Grease	11.000 1/min	Limiting speed for grease lubrication
$n_{G\text{ Oil}}$	18.000 1/min	Limiting speed for oil lubrication
$\approx m$	0,59 kg	Weight





Mounting dimensions

d_a	77 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	102 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	0,6 mm	Maximum recess radius
$E_{tk \min}$	82,4 mm	Minimum diameter injection pitch
$E_{tk \max}$	86,7 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	82,4 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	86,7 mm	Maximum diameter injection pitch
a	31 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
$r_{1 \min}$	1,1 mm	Minimum chamfer dimension
α	25 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.



Additional information

F_{VL}	395 N	Preload force light
F_{VM}	1.388 N	Preload force medium
F_{VH}	2.915 N	Preload force heavy
K_{aEL}	1.149 N	Lift-off force light
K_{aEM}	4.183 N	Lift-off force medium
K_{aEH}	9.083 N	Lift-off force heavy
c_{aL}	169 N/ μ m	Axial rigidity light
c_{aM}	273 N/ μ m	Axial rigidity medium
c_{aH}	371 N/ μ m	Axial rigidity heavy

Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed