

**FAG****B7022-E-T-P4S-UL**

Spindle bearing

Spindle bearing B70..-E, adjusted, in pairs or sets, contact angle $\alpha = 25^\circ$, restricted tolerances

Technical information





Your current product variant

Preload	L	Preload light
Contact angle	E	Contact angle 25°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Type of Seal	Without	Not sealed
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	170 mm	Outside diameter
B	28 mm	Width
C_r	106.000 N	Basic dynamic load rating, radial
C_{0r}	73.000 N	Basic static load rating, radial
C_{ur}	6.600 N	Fatigue load limit, radial
n_G Grease	7.500 1/min	Limiting speed for grease lubrication
$n_{G\text{ Oil}}$	12.000 1/min	Limiting speed for oil lubrication
$\approx m$	1,925 kg	Weight





Mounting dimensions

d_a	121 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	159 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	2 mm	Maximum recess radius
$r_{a1 \max}$	1 mm	Maximum recess radius
$E_{tk \min}$	128,6 mm	Minimum diameter injection pitch
$E_{tk \max}$	135,1 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	128,6 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	135,1 mm	Maximum diameter injection pitch
a	46,6 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	2 mm	Minimum chamfer dimension
$r_{1 \min}$	2 mm	Minimum chamfer dimension
α	25 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.



Additional information

F_{VL}	968 N	Preload force light
F_{VM}	3.242 N	Preload force medium
F_{VH}	6.709 N	Preload force heavy
K_{aEL}	2.820 N	Lift-off force light
K_{aEM}	9.745 N	Lift-off force medium
K_{aEH}	20.814 N	Lift-off force heavy
c_{aL}	280 N/μm	Axial rigidity light
c_{aM}	443 N/μm	Axial rigidity medium
c_{aH}	596 N/μm	Axial rigidity heavy

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed