
**FAG****B71932-E-T-P4S-UL**

## Spindle bearing

Spindle bearing B719...-E, adjusted, in pairs or sets, contact angle  $\alpha = 25^\circ$ , restricted tolerances

## Technical information





## Your current product variant

|                         |         |                                                                  |
|-------------------------|---------|------------------------------------------------------------------|
| Preload                 | L       | Preload light                                                    |
| Contact angle           | E       | Contact angle $25^\circ$                                         |
| Tolerance class         | P4S     | Tolerance class P4S, FAG standard better than P4 to ISO 492:2023 |
| Sealing                 | Without | Not sealed                                                       |
| Cage                    | T       | Laminated fabric cage                                            |
| Arrangement bearing set | U       | Single bearing                                                   |

## Main Dimensions &amp; Performance Data

|                        |             |                                       |
|------------------------|-------------|---------------------------------------|
| d                      | 160 mm      | Bore diameter                         |
| D                      | 220 mm      | Outside diameter                      |
| B                      | 28 mm       | Width                                 |
| $C_r$                  | 121.000 N   | Basic dynamic load rating, radial     |
| $C_{0r}$               | 100.000 N   | Basic static load rating, radial      |
| $C_{ur}$               | 7.700 N     | Fatigue load limit, radial            |
| $n_{G \text{ Grease}}$ | 5.300 1/min | Limiting speed for grease lubrication |
| $n_{G \text{ Oil}}$    | 8.000 1/min | Limiting speed for oil lubrication    |
| $\approx m$            | 2,587 kg    | Weight                                |





### Mounting dimensions

|                |          |                                                   |
|----------------|----------|---------------------------------------------------|
| $d_a$          | 170 mm   | Diameter shaft shoulder                           |
| $d_a$          | h12      | Diameter shaft shoulder clearance                 |
| $D_a$          | 209 mm   | Shoulder diameter outer ring                      |
| $D_a$          | H12      | Shoulder diameter outer ring clearance            |
| $r_{a \max}$   | 1 mm     | Maximum recess radius                             |
| $r_{a1 \max}$  | 1 mm     | Maximum recess radius                             |
| $E_{tk \min}$  | 179,5 mm | Minimum diameter injection pitch                  |
| $E_{tk \max}$  | 184,7 mm | Maximum diameter injection pitch                  |
| $E_{tk1 \min}$ | 179,5 mm | Minimum diameter injection pitch                  |
| $E_{tk1 \max}$ | 184,7 mm | Maximum diameter injection pitch                  |
| $a$            | 58,3 mm  | Distance between the apexes of the pressure cones |

### Dimensions

|              |      |                           |
|--------------|------|---------------------------|
| $r_{\min}$   | 2 mm | Minimum chamfer dimension |
| $r_{1 \min}$ | 1 mm | Minimum chamfer dimension |
| $\alpha$     | 25 ° | Contact angle             |

### Temperature range

|            |        |                            |
|------------|--------|----------------------------|
| $T_{\min}$ | -30 °C | Operating temperature min. |
| $T_{\max}$ | 100 °C | Operating temperature max. |



Additional information

|           |                |                       |
|-----------|----------------|-----------------------|
| $F_{VL}$  | 1.055 N        | Preload force light   |
| $F_{VM}$  | 3.579 N        | Preload force medium  |
| $F_{VH}$  | 7.439 N        | Preload force heavy   |
| $K_{aEL}$ | 3.062 N        | Lift-off force light  |
| $K_{aEM}$ | 10.696 N       | Lift-off force medium |
| $K_{aEH}$ | 22.899 N       | Lift-off force heavy  |
| $c_{aL}$  | 341 N/ $\mu$ m | Axial rigidity light  |
| $c_{aM}$  | 539 N/ $\mu$ m | Axial rigidity medium |
| $c_{aH}$  | 725 N/ $\mu$ m | Axial rigidity heavy  |

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed