
**FAG****B71948-E-T-P4S-UL**

Spindle bearing

Spindle bearing B719...-E, adjusted, in pairs or sets, contact angle $\alpha = 25^\circ$, restricted tolerances

Technical information





Your current product variant

Preload	L	Preload light
Contact angle	E	Contact angle 25°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	Without	Not sealed
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing

Main Dimensions & Performance Data

d	240 mm	Bore diameter
D	320 mm	Outside diameter
B	38 mm	Width
C_r	218.000 N	Basic dynamic load rating, radial
C_{0r}	208.000 N	Basic static load rating, radial
C_{ur}	13.100 N	Fatigue load limit, radial
n_G Grease	3.600 1/min	Limiting speed for grease lubrication
$n_{G\text{ Oil}}$	5.300 1/min	Limiting speed for oil lubrication
$\approx m$	6,997 kg	Weight





Mounting dimensions

d_a	254 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	307 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	1 mm	Maximum recess radius
$E_{tk \min}$	264,7 mm	Minimum diameter injection pitch
$E_{tk \max}$	272,9 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	264,7 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	272,9 mm	Maximum diameter injection pitch
a	84,3 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
$r_{1 \min}$	1,1 mm	Minimum chamfer dimension
α	25 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.



Additional information

F_{VL}	1.760 N	Preload force light
F_{VM}	6.279 N	Preload force medium
F_{VH}	13.255 N	Preload force heavy
K_{aEL}	5.092 N	Lift-off force light
K_{aEM}	18.673 N	Lift-off force medium
K_{aEH}	40.536 N	Lift-off force heavy
c_{aL}	488 N/ μ m	Axial rigidity light
c_{aM}	781 N/ μ m	Axial rigidity medium
c_{aH}	1.052 N/ μ m	Axial rigidity heavy

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed
- 

Large bearing