




FAG

B71936-C-T-P4S-UL

Spindle bearing

Spindle bearing B719...-C, adjusted, in pairs or sets, contact angle $\alpha = 15^\circ$, restricted tolerances

Technical information



Your current product variant

Preload	L	Preload light
Contact angle	C	Contact angle 15°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	Without	Not sealed
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing

Main Dimensions & Performance Data

d	180 mm	Bore diameter
D	250 mm	Outside diameter
B	33 mm	Width
C _r	171.000 N	Basic dynamic load rating, radial
C _{0r}	146.000 N	Basic static load rating, radial
C _{ur}	10.500 N	Fatigue load limit, radial
n _{G Grease}	5.300 1/min	Limiting speed for grease lubrication
n _{G Oil}	8.000 1/min	Limiting speed for oil lubrication
≈m	4,065 kg	Weight



Mounting dimensions

d_a	192 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	238 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	1 mm	Maximum recess radius
$E_{tk \min}$	201,6 mm	Minimum diameter injection pitch
$E_{tk \max}$	209 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	201,6 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	209 mm	Maximum diameter injection pitch
a	45,3 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	2 mm	Minimum chamfer dimension
$r_{1 \min}$	1 mm	Minimum chamfer dimension
α	15 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.



Additional information

F_{VL}	960 N	Preload force light
F_{VM}	3.036 N	Preload force medium
F_{VH}	6.076 N	Preload force heavy
K_{aEL}	2.933 N	Lift-off force light
K_{aEM}	9.953 N	Lift-off force medium
K_{aEH}	21.191 N	Lift-off force heavy
c_{aL}	168 N/ μ m	Axial rigidity light
c_{aM}	279 N/ μ m	Axial rigidity medium
c_{aH}	394 N/ μ m	Axial rigidity heavy

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed