


**FAG****B71908-E-2RSD-T-P4S-UL**

Spindle bearing

Spindle bearing B719...-E-2RSD, adjusted, in pairs or sets, contact angle $\alpha = 25^\circ$, lip seals on both sides, non-contact, restricted tolerances

Technical information



Your current product variant

Preload	L	Preload light
Contact angle	E	Contact angle 25°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	2RSD	Non-contact sealed on both sides and greased "for life"
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing
Lubricant	GA21	Grease for super precision bearings, standard

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	62 mm	Outside diameter
B	12 mm	Width
C _r	17.100 N	Basic dynamic load rating, radial
C _{0r}	9.400 N	Basic static load rating, radial
C _{ur}	990 N	Fatigue load limit, radial
n _G Grease	20.000 1/min	Limiting speed for grease lubrication
≈m	107,9 g	Weight



Mounting dimensions

d_a	45 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	58,5 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	0,6 mm	Maximum recess radius
$r_{a1 \max}$	0,15 mm	Maximum recess radius
a	17,9 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
$r_{1 \min}$	0,6 mm	Minimum chamfer dimension
α	25 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	80 °C	Operating temperature max.

Additional information

F_{VL}	111 N	Preload force light
F_{VM}	447 N	Preload force medium
F_{VH}	974 N	Preload force heavy
K_{aEL}	324 N	Lift-off force light
K_{aEM}	1.348 N	Lift-off force medium
K_{aEH}	3.043 N	Lift-off force heavy
c_{aL}	91 N/μm	Axial rigidity light
c_{aM}	155 N/μm	Axial rigidity medium
c_{aH}	213 N/μm	Axial rigidity heavy



Characteristics

-  Radial load
-  Axial load in one direction
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides