
**FAG****HS71905-C-T-P4S-UL**

High speed spindle bearing

High speed spindle bearing HS719...-C,
adjusted, in pairs or sets, contact angle $\alpha = 15^\circ$, restricted tolerances

Technical information





Your current product variant

Contact angle	C	Contact angle 15°
Type of Seal	Without	Not sealed
Cage	T	Laminated fabric cage
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Arrangement bearing set	U	Single bearing
Preload	L	Preload light

Main Dimensions & Performance Data

d	25 mm	Bore diameter
D	42 mm	Outside diameter
B	9 mm	Width
C_r	3.900 N	Basic dynamic load rating, radial
C_{0r}	2.060 N	Basic static load rating, radial
C_{ur}	218 N	Fatigue load limit, radial
n_G Grease	48.000 1/min	Limiting speed for grease lubrication
n_G Oil	75.000 1/min	Limiting speed for oil lubrication
n_G	75.000 1/min	Limiting speed
$\approx m$	43,7 g	Weight





Mounting dimensions

d_a	29 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	38,5 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	0,3 mm	Maximum recess radius
$r_{a1 \max}$	0,15 mm	Maximum recess radius
$E_{tk \min}$	31,6 mm	Minimum diameter injection pitch
$E_{tk \max}$	32,2 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	30,4 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	32,2 mm	Maximum diameter injection pitch
a	9 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	0,3 mm	Minimum chamfer dimension
$r_{1 \min}$	0,3 mm	Minimum chamfer dimension
α	15 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.



Additional information

F_{VL}	14 N	Preload force light
F_{VM}	43 N	Preload force medium
F_{VH}	85 N	Preload force heavy
K_{aEL}	43 N	Lift-off force light
K_{aEM}	135 N	Lift-off force medium
K_{aEH}	282 N	Lift-off force heavy
c_{aL}	17 N/μm	Axial rigidity light
c_{aM}	27 N/μm	Axial rigidity medium
c_{aH}	37 N/μm	Axial rigidity heavy

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed