
**FAG****B71920-E-T-P4S-UL**

Spindle bearing

Spindle bearing B719...-E, adjusted, in pairs or sets, contact angle $\alpha = 25^\circ$, restricted tolerances

Technical information





Your current product variant

Preload	L	Preload light
Contact angle	E	Contact angle 25°
Tolerance class	P4S	Tolerance class P4S, FAG standard better than P4 to ISO 492:2023
Sealing	Without	Not sealed
Cage	T	Laminated fabric cage
Arrangement bearing set	U	Single bearing

Main Dimensions & Performance Data

d	100 mm	Bore diameter
D	140 mm	Outside diameter
B	20 mm	Width
C_r	57.000 N	Basic dynamic load rating, radial
C_{0r}	42.500 N	Basic static load rating, radial
C_{ur}	4.100 N	Fatigue load limit, radial
$n_{G \text{ Grease}}$	8.500 1/min	Limiting speed for grease lubrication
$n_{G \text{ Oil}}$	13.000 1/min	Limiting speed for oil lubrication
$\approx m$	0,78 kg	Weight





Mounting dimensions

d_a	107 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	133 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	0,6 mm	Maximum recess radius
$r_{a1 \max}$	0,6 mm	Maximum recess radius
$E_{tk \min}$	113,4 mm	Minimum diameter injection pitch
$E_{tk \max}$	117,5 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	113,4 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	117,5 mm	Maximum diameter injection pitch
a	38,2 mm	Distance between the apexes of the pressure cones

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
$r_{1 \min}$	1,1 mm	Minimum chamfer dimension
α	25 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.



Additional information

F_{VL}	450 N	Preload force light
F_{VM}	1.616 N	Preload force medium
F_{VH}	3.417 N	Preload force heavy
K_{aEL}	1.305 N	Lift-off force light
K_{aEM}	4.839 N	Lift-off force medium
K_{aEH}	10.556 N	Lift-off force heavy
c_{aL}	219 N/ μ m	Axial rigidity light
c_{aM}	353 N/ μ m	Axial rigidity medium
c_{aH}	479 N/ μ m	Axial rigidity heavy

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed