

**FAG****1220-M**

Self-aligning ball bearing

Self-aligning ball bearing 12..-M, solid brass cage

Technical information



Your current product variant

Bore type	Z	Cylindrical
Type of Sealing	Without	Not sealed
Cage	M	Solid brass cage, ball guided
Tolerance class	PN	Normal (ISO 492:2023)
Radial internal clearance	CN (Group N)	Normal internal clearance
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	100 mm	Bore diameter
D	180 mm	Outside diameter
B	34 mm	Width
C _r	70.000 N	Basic dynamic load rating, radial
C _{0r}	29.500 N	Basic static load rating, radial
C _{ur}	1.590 N	Fatigue load limit, radial
n _G	6.000 1/min	Limiting speed
n _{gr}	4.500 1/min	Reference speed
m	3,606 kg	Weight

Mounting dimensions

d _{a min}	112 mm	Minimum diameter shaft shoulder
D _{a max}	168 mm	Maximum diameter of housing shoulder
r _{a max}	2,1 mm	Maximum fillet radius



Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
D_1	155,2 mm	Shoulder diameter outer ring
d_1	127,3 mm	Shoulder diameter inner ring

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	150 °C	Operating temperature max.

Calculation factors

e	0,18	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	3,58	Dynamic axial load factor
Y_2	5,53	Dynamic axial load factor
Y_0	3,75	Static axial load factor

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Static angular error and misalignment
	Dynamic angular error and misalignment