


**FAG****1306-K-TVH-C3** [🔗](#)

Self-aligning ball bearing

Self-aligning ball bearing 13..-K-TVH, tapered bore taper 1:12, plastic cage

Technical information



Your current product variant

Bore type	K	Tapered, taper 1:12
Sealing	Without	Not sealed
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	PN	Normal (ISO 492:2023)
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	30 mm	Bore diameter
D	72 mm	Outside diameter
B	19 mm	Width
C _r	21.700 N	Basic dynamic load rating, radial
C _{0r}	6.300 N	Basic static load rating, radial
C _{ur}	400 N	Fatigue load limit, radial
n _G	11.100 1/min	Limiting speed
n _{gr}	8.700 1/min	Reference speed
≈m	0,379 kg	Weight



Mounting dimensions

$d_{a \min}$	37 mm	Minimum diameter shaft shoulder
$d_{a \max}$	42 mm	Maximum diameter shaft shoulder
$D_{a \max}$	65 mm	Maximum diameter of housing shoulder
$d_{b \min}$	33 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	6 mm	Minimum cavity width of the sleeve
$r_{a \max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
D_1	58,93 mm	Shoulder diameter outer ring
d_1	45,1 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

e	0,26	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,41	Dynamic axial load factor
Y_2	3,72	Dynamic axial load factor
Y_0	2,52	Static axial load factor

Additional information

H306

Adapter sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment