






FAG

1322-K-M-C3

Self-aligning ball bearing

Self-aligning ball bearing 13..-K-M, tapered bore taper 1:12, solid brass cage

Technical information




Your current product variant

Bore type	K	Tapered, taper 1:12
Sealing	Without	Not sealed
Cage	M	Solid brass cage, ball guided
Tolerance class	PN	Normal (ISO 492:2023)
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	240 mm	Outside diameter
B	50 mm	Width
C _r	165.000 N	Basic dynamic load rating, radial
C _{0r}	72.000 N	Basic static load rating, radial
C _{ur}	3.400 N	Fatigue load limit, radial
n _G	4.200 1/min	Limiting speed
n _{gr}	3.400 1/min	Reference speed
≈m	11,767 kg	Weight



Mounting dimensions

$d_{a \min}$	124 mm	Minimum diameter shaft shoulder
$d_{a \max}$	150 mm	Maximum diameter shaft shoulder
$D_{a \max}$	226 mm	Maximum diameter of housing shoulder
$d_{b \min}$	118 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	9 mm	Minimum cavity width of the sleeve
$r_{a \max}$	2,5 mm	Maximum fillet radius

Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
D_1	202,5 mm	Shoulder diameter outer ring
d_1	154,46 mm	Shoulder diameter inner ring
C_1	2,7 mm	Overhang rolling element

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.

Calculation factors

e	0,23	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,78	Dynamic axial load factor
Y_2	4,3	Dynamic axial load factor
Y_0	2,91	Static axial load factor

Additional information

H322

Adapter sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment