

**FAG****1301-TVH**

Self-aligning ball bearing

Self-aligning ball bearing 13...TVH, plastic cage

Technical information



Your current product variant

Bore type	Z	Cylindrical
Type of Seal	Without	Not sealed
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	PN	Normal (ISO 492:2023)
Radial internal clearance	CN (Group N)	Normal internal clearance
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	12 mm	Bore diameter
D	37 mm	Outside diameter
B	12 mm	Width
C _r	9.800 N	Basic dynamic load rating, radial
C _{0r}	2.160 N	Basic static load rating, radial
C _{ur}	137 N	Fatigue load limit, radial
n _G	22.300 1/min	Limiting speed
n _{gr}	16.200 1/min	Reference speed
≈m	0,06 kg	Weight

Mounting dimensions

d _{a min}	17,6 mm	Minimum diameter shaft shoulder
D _{a max}	31,4 mm	Maximum diameter of housing shoulder
r _{a max}	1 mm	Maximum fillet radius



Dimensions

r_{min}	1 mm	Minimum chamfer dimension
D_1	29,7 mm	Shoulder diameter outer ring
d_1	20,29 mm	Shoulder diameter inner ring

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.

Calculation factors

e	0,35	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	1,8	Dynamic axial load factor
Y_2	2,79	Dynamic axial load factor
Y_0	1,89	Static axial load factor

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Axial load in two directions
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed
- 

Static angular error and misalignment
- 

Dynamic angular error and misalignment