


**FAG****2209-K-TVH-C3**

Self-aligning ball bearing

Self-aligning ball bearing 22...-K-TVH, tapered bore taper 1:12, plastic cage

Technical information



Your current product variant

Bore type	K	Tapered, taper 1:12
Type of Seal	Without	Not sealed
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	PN	Normal (ISO 492:2023)
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	45 mm	Bore diameter
D	85 mm	Outside diameter
B	23 mm	Width
C _r	28.500 N	Basic dynamic load rating, radial
C _{0r}	9.000 N	Basic static load rating, radial
C _{ur}	570 N	Fatigue load limit, radial
n _G	8.600 1/min	Limiting speed
n _{gr}	7.800 1/min	Reference speed
≈m	0,533 kg	Weight



Mounting dimensions

$d_{a \min}$	52 mm	Minimum diameter shaft shoulder
$d_{a \max}$	56 mm	Maximum diameter shaft shoulder
$D_{a \max}$	78 mm	Maximum diameter of housing shoulder
$d_{b \min}$	50 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	7 mm	Minimum cavity width of the sleeve
$r_{a \max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
D_1	75,41 mm	Shoulder diameter outer ring
d_1	58,95 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

e	0,26	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,43	Dynamic axial load factor
Y_2	3,76	Dynamic axial load factor
Y_0	2,55	Static axial load factor

Additional information

H309

Adapter sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment