




**FAG****2308-K-TVH-C3**

Self-aligning ball bearing

Self-aligning ball bearing 23...-K-TVH, tapered bore taper 1:12, plastic cage

Technical information



Your current product variant

Bore type	K	Tapered, taper 1:12
Type of Seal	Without	Not sealed
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	PN	Normal (ISO 492:2023)
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	90 mm	Outside diameter
B	33 mm	Width
C _r	46.000 N	Basic dynamic load rating, radial
C _{0r}	13.500 N	Basic static load rating, radial
C _{ur}	860 N	Fatigue load limit, radial
n _G	7.900 1/min	Limiting speed
n _{gr}	8.700 1/min	Reference speed
≈m	0,89 kg	Weight



Mounting dimensions

d _{a min}	49 mm	Minimum diameter shaft shoulder
d _{a max}	51 mm	Maximum diameter shaft shoulder
D _{a max}	81 mm	Maximum diameter of housing shoulder
d _{b min}	45 mm	Minimum cavity diameter of the sleeve
B _{a min}	5 mm	Minimum cavity width of the sleeve
r _{a max}	1,5 mm	Maximum fillet radius

Dimensions

r _{min}	1,5 mm	Minimum chamfer dimension
D ₁	74,51 mm	Shoulder diameter outer ring
d ₁	53,7 mm	Shoulder diameter inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0,43	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	1,46	Dynamic axial load factor
Y ₂	2,25	Dynamic axial load factor
Y ₀	1,52	Static axial load factor

Additional information

H2308	Adapter sleeve
-------	----------------



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment