



FAG




NU2210-E-XL-TVP2

Cylindrical roller bearing

Cylindrical roller bearing NU..-E-XL-TVP2,
with cage, single row, non-locating bearing,
2 ribs on outer ring, 0 ribs on inner ring
(smooth), type NU, Running accuracy in P6

X-life

Technical information



Your current product variant

Design	E	Increased Capacity Design
Cage	TVP2	Solid Window Cage made from PA66
Radial internal clearance	CN (Group N)	Normal internal clearance
Tolerance class	PN	Normal (ISO 492:2023)
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	90 mm	Outside diameter
B	23 mm	Width
C _r	92.000 N	Basic dynamic load rating, radial
C _{0r}	88.000 N	Basic static load rating, radial
C _{ur}	15.300 N	Fatigue load limit, radial
n _G	11.100 1/min	Limiting speed
n _{gr}	5.300 1/min	Reference speed
m	0,553 kg	Weight



Mounting dimensions

d a min	57 mm	Minimum diameter shaft shoulder
d a max	58 mm	Maximum diameter of shaft shoulder
d b min	62 mm	Minimum shaft shoulder
D a max	83 mm	Maximum diameter of housing shoulder
r a max	1 mm	Maximum recess radius
r a1 max	1 mm	Maximum recess radius

Dimensions

r min	1,1 mm	Minimum chamfer dimension
r 1 min	1,1 mm	Minimum chamfer dimension
s	1,3 mm	Axial displacement
E	81,5 mm	Raceway diameter outer ring
F	59,5 mm	Raceway diameter inner ring
D 1 min	78,3 mm	Minimum rib diameter outer ring

Temperature range

T min	-30 °C	Operating temperature min.
T max	120 °C	Operating temperature max.

Characteristics

	Radial load
	Grease Lubrication
	Oil Lubrication
	Not sealed