

**FAG****11209-TVH**

Self-aligning ball bearing

Self-aligning ball bearing 112...-TVH, plastic cage

## Technical information



## Your current product variant

|      |     |                                                          |
|------|-----|----------------------------------------------------------|
| Cage | TVH | Solid cage made of glass-fiber reinforced polyamide PA66 |
|------|-----|----------------------------------------------------------|

## Main Dimensions &amp; Performance Data

|                 |             |                                   |
|-----------------|-------------|-----------------------------------|
| d               | 45 mm       | Bore diameter                     |
| D               | 85 mm       | Outside diameter                  |
| B               | 58 mm       | Total width                       |
| B <sub>C</sub>  | 19 mm       | Width, outer ring                 |
| B <sub>i</sub>  | 58 mm       | Width, inner ring                 |
| C <sub>r</sub>  | 22.000 N    | Basic dynamic load rating, radial |
| C <sub>0r</sub> | 7.300 N     | Basic static load rating, radial  |
| C <sub>ur</sub> | 465 N       | Fatigue load limit, radial        |
| n <sub>G</sub>  | 9.300 1/min | Limiting speed                    |
| n <sub>gr</sub> | 8.200 1/min | Reference speed                   |
| ≈m              | 0,788 kg    | Weight                            |

## Mounting dimensions

|                    |       |                                      |
|--------------------|-------|--------------------------------------|
| D <sub>a max</sub> | 78 mm | Maximum diameter of housing shoulder |
| r <sub>a max</sub> | 1 mm  | Maximaler Hohlkehlradius             |



Dimensions

|           |          |                              |
|-----------|----------|------------------------------|
| $r_{min}$ | 1,1 mm   | Minimum chamfer dimension    |
| $D_1$     | 72,11 mm | Shoulder diameter outer ring |
| $d_1$     | 57,7 mm  | Shoulder diameter inner ring |
| $b$       | 7 mm     | Width retaining slot         |
| $t$       | 9 mm     | Hight retaining slot         |

Temperature range

|           |        |                            |
|-----------|--------|----------------------------|
| $T_{min}$ | -30 °C | Operating temperature min. |
| $T_{max}$ | 120 °C | Operating temperature max. |

Calculation factors

|       |      |                                                                                      |
|-------|------|--------------------------------------------------------------------------------------|
| $e$   | 0,21 | Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y |
| $Y_1$ | 3,03 | Dynamic axial load factor                                                            |
| $Y_2$ | 4,68 | Dynamic axial load factor                                                            |
| $Y_0$ | 3,17 | Static axial load factor                                                             |

Characteristics

|                                                                                     |                                        |
|-------------------------------------------------------------------------------------|----------------------------------------|
|  | Radial load                            |
|  | Axial load in one direction            |
|  | Axial load in two directions           |
|  | Grease Lubrication                     |
|  | Oil Lubrication                        |
|  | Not sealed                             |
|  | Static angular error and misalignment  |
|  | Dynamic angular error and misalignment |