



FAG



X-life

QJ313-XL-MPA-C3

Four-point contact bearing

Four point contact bearing QJ3...-XL-MPA, X-life, solid brass cage

Technical information



Your current product variant

Tolerance class	PN	Normal (ISO 492:2023)
Cage	MPA	Solid brass cage, outer ring guided
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Axial internal clearance	C3	Group 3 (C3), bigger than CN

Main Dimensions & Performance Data

d	65 mm	Bore diameter
D	140 mm	Outside diameter
B	33 mm	Width
C _r	171.000 N	Basic dynamic load rating, radial
C _{0r}	145.000 N	Basic static load rating, radial
C _{ur}	10.800 N	Fatigue load limit, radial
n _G	9.600 1/min	Limiting speed
n _{gr}	4.450 1/min	Reference speed
≈m	2,59 kg	Weight

Mounting dimensions

d _{a min}	77 mm	Minimum diameter shaft shoulder
D _{a max}	128 mm	Maximum diameter of housing shoulder
r _{a max}	2,1 mm	Maximum fillet radius



Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
D_1	114,4 mm	Shoulder diameter outer ring
d_1	90,96 mm	Shoulder diameter inner ring
a	71,8 mm	Distance between the apexes of the pressure cones
α	35 °	Contact angle

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	150 °C	Operating temperature max.

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed