




**FAG****NU2238-E-M1-C3**

Cylindrical roller bearing

Cylindrical roller bearing NU..-E-M1, with cage, single row, non-locating bearing, 2 ribs on outer ring, 0 ribs on inner ring (smooth), type NU, Running accuracy in P6

Technical information



Your current product variant

Design	E	Increased Capacity Design
Cage	M1	Two Piece Brass Cage Roller Guided
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Tolerance class	PN	Normal (ISO 492:2023)
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	190 mm	Bore diameter
D	340 mm	Outside diameter
B	92 mm	Width
C _r	1.090.000 N	Basic dynamic load rating, radial
C _{0r}	1.650.000 N	Basic static load rating, radial
C _{ur}	206.000 N	Fatigue load limit, radial
n _G	3.000 1/min	Limiting speed
n _{gr}	1.290 1/min	Reference speed
≈m	36,48 kg	Weight



Mounting dimensions

d a min	207 mm	Minimum diameter shaft shoulder
d a max	227 mm	Maximum diameter of shaft shoulder
d b min	234 mm	Minimum shaft shoulder
D a max	323 mm	Maximum diameter of housing shoulder
r a max	3 mm	Maximum recess radius
r a1 max	3 mm	Maximum recess radius

Dimensions

r min	4 mm	Minimum chamfer dimension
r 1 min	4 mm	Minimum chamfer dimension
s	8 mm	Axial displacement
E	308 mm	Raceway diameter outer ring
F	228 mm	Raceway diameter inner ring
D 1 min	296,4 mm	Minimum rib diameter outer ring

Temperature range

T min	-30 °C	Operating temperature min.
T max	150 °C	Operating temperature max.

Characteristics

	Radial load
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Large bearing