


**FAG****30203-A**

## Tapered roller bearing

Tapered roller bearings 302, main dimensions  
acc. to DIN 720, separable

## Technical information



## Your current product variant

|                 |          |                                              |
|-----------------|----------|----------------------------------------------|
| Tolerance class | PN       | Normal (ISO 492:2023)                        |
| Heat treatment  | Standard |                                              |
| Cage            | Standard | Sheet steel cage, window cage, roller-guided |
| Internal design | Standard |                                              |
| Quality level   | Standard |                                              |
| Number of rows  | 1        | Single-row design                            |

## Main Dimensions &amp; Performance Data

|          |              |                                   |
|----------|--------------|-----------------------------------|
| d        | 17 mm        | Bore diameter                     |
| D        | 40 mm        | Outside diameter                  |
| B        | 12 mm        | Width, inner ring                 |
| C        | 11 mm        | Width, outer ring                 |
| T        | 13,25 mm     | Width, total                      |
| $C_r$    | 19.200 N     | Basic dynamic load rating, radial |
| $C_{0r}$ | 18.700 N     | Basic static load rating, radial  |
| $C_{ur}$ | 1.900 N      | Fatigue load limit, radial        |
| $n_G$    | 20.100 1/min | Limiting speed                    |
| $n_{gr}$ | 11.800 1/min | Thermal speed rating              |
| $m$      | 77,7 g       | Weight                            |



### Mounting dimensions

|              |       |                                      |
|--------------|-------|--------------------------------------|
| $d_{a \max}$ | 23 mm | Maximum diameter of shaft shoulder   |
| $d_{b \min}$ | 23 mm | Minimum diameter of shaft shoulder   |
| $D_{a \min}$ | 34 mm | Minimum diameter of housing shoulder |
| $D_{a \max}$ | 34 mm | Maximum diameter of housing shoulder |
| $D_{b \min}$ | 37 mm | Minimum diameter of housing shoulder |
| $C_{a \min}$ | 2 mm  | Minimum axial space                  |
| $C_{b \min}$ | 2 mm  | Minimum axial space                  |
| $r_{a \max}$ | 1 mm  | Maximum fillet radius of shaft       |
| $r_{b \max}$ | 1 mm  | Maximum fillet radius of housing     |

### Dimensions

|                 |         |                                                   |
|-----------------|---------|---------------------------------------------------|
| $r_{1, 2 \min}$ | 1 mm    | Minimum chamfer dimension of inner ring back face |
| $r_{3, 4 \min}$ | 1 mm    | Minimum chamfer dimension of outer ring back face |
| $a$             | 10 mm   | Distance between the apexes of the pressure cones |
| $d_1$           | 29,1 mm | Guidance rib diameter of inner ring               |

### Temperature range

|            |        |                            |
|------------|--------|----------------------------|
| $T_{\min}$ | -30 °C | Operating temperature min. |
| $T_{\max}$ | 120 °C | Operating temperature max. |

### Calculation factors

|       |      |                                                                                      |
|-------|------|--------------------------------------------------------------------------------------|
| $e$   | 0,35 | Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y |
| $Y$   | 1,74 | Dynamic axial load factor                                                            |
| $Y_0$ | 0,96 | Static axial load factor                                                             |

### Additional information

T2DB017

Comparative designation to ISO 10317 and ISO 355



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed