




**FAG****X-life****NUP2204-E-XL-TVP2**

Cylindrical roller bearing

Cylindrical roller bearing NUP...-E-XL-TVP2, with cage, single row, locating bearing, 2 ribs on outer ring, 1 rib on inner ring, rib washer internal, type NUP

Technical information



Your current product variant

Design	E	Increased Capacity Design
Cage	TVP2	Solid Window Cage made from PA66
Radial internal clearance	CN (Group N)	Normal internal clearance
Tolerance class	PN	Normal (ISO 492:2023)
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	20 mm	Bore diameter
D	47 mm	Outside diameter
B	18 mm	Width
C _r	38.500 N	Basic dynamic load rating, radial
C _{0r}	31.000 N	Basic static load rating, radial
C _{ur}	5.200 N	Fatigue load limit, radial
n _G	22.000 1/min	Limiting speed
n _{gr}	11.100 1/min	Reference speed
≈m	0,149 kg	Weight



Mounting dimensions

d ₁	29,7 mm	Maximum rib diameter inner ring
D _{1 min}	38,8 mm	Minimum rib diameter outer ring
d _{a min}	24 mm	Minimum diameter shaft shoulder
d _{c min}	32 mm	Minimum shaft shoulder
D _{a max}	41 mm	Maximum diameter of housing shoulder
r _{a max}	1 mm	Maximum recess radius

Dimensions

r _{min}	1 mm	Minimum chamfer dimension
r _{1 min}	0,6 mm	Minimum chamfer dimension
E	41,5 mm	Raceway diameter outer ring
F	26,5 mm	Raceway diameter inner ring
B ₃	3,5 mm	Width of loose rib

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed