




FAG

33208

Tapered roller bearing

Tapered roller bearings 332, main dimensions
acc. to DIN 720, separable

Technical information



Your current product variant

Tolerance class	P6X	Class 6X (ISO 492:2023)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	Standard	
Quality level	Standard	
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	80 mm	Outside diameter
B	32 mm	Width, inner ring
C	25 mm	Width, outer ring
T	32 mm	Width, total
C _r	105.000 N	Basic dynamic load rating, radial
C _{0r}	134.000 N	Basic static load rating, radial
C _{ur}	16.900 N	Fatigue load limit, radial
n _G	9.000 1/min	Limiting speed
n _{gr}	5.700 1/min	Thermal speed rating
≈m	0,735 kg	Weight



Mounting dimensions

d _a max	47 mm	Maximum diameter of shaft shoulder
d _b min	47 mm	Minimum diameter of shaft shoulder
D _a min	67 mm	Minimum diameter of housing shoulder
D _a max	73 mm	Maximum diameter of housing shoulder
D _b min	76 mm	Minimum diameter of housing shoulder
C _a min	5 mm	Minimum axial space
C _b min	7 mm	Minimum axial space
r _a max	1,5 mm	Maximum fillet radius of shaft
r _b max	1,5 mm	Maximum fillet radius of housing

Dimensions

r _{1, 2} min	1,5 mm	Minimum chamfer dimension of inner ring back face
r _{3, 4} min	1,5 mm	Minimum chamfer dimension of outer ring back face
a	21 mm	Distance between the apexes of the pressure cones
d ₁	60,7 mm	Guidance rib diameter of inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0,36	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	1,68	Dynamic axial load factor
Y ₀	0,92	Static axial load factor

Additional information

T2DE040	Comparative designation to ISO 10317 and ISO 355
---------	--



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed