



FAG


32205-XL

Tapered roller bearing

Tapered roller bearings 322, main dimensions
acc. to DIN 720, separable

X-life

Technical information



Your current product variant

Tolerance class	PN	Normal (ISO 492:2023)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	Standard	
Quality level	XL	X-life
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	25 mm	Bore diameter
D	52 mm	Outside diameter
B	18 mm	Width, inner ring
C	16 mm	Width, outer ring
T	19,25 mm	Width, total
C _r	50.000 N	Basic dynamic load rating, radial
C _{0r}	45.000 N	Basic static load rating, radial
C _{ur}	6.800 N	Fatigue load limit, radial
n _G	17.500 1/min	Limiting speed
n _{gr}	8.000 1/min	Thermal speed rating
m	184,6 g	Weight



Mounting dimensions

d _a max	31 mm	Maximum diameter of shaft shoulder
d _b min	31 mm	Minimum diameter of shaft shoulder
D _a min	44 mm	Minimum diameter of housing shoulder
D _a max	46 mm	Maximum diameter of housing shoulder
D _b min	48 mm	Minimum diameter of housing shoulder
C _a min	3 mm	Minimum axial space
C _b min	4 mm	Minimum axial space
r _a max	1 mm	Maximum fillet radius of shaft
r _b max	1 mm	Maximum fillet radius of housing

Dimensions

r _{1, 2} min	1 mm	Minimum chamfer dimension of inner ring back face
r _{3, 4} min	1 mm	Minimum chamfer dimension of outer ring back face
a	14 mm	Distance between the apexes of the pressure cones
d ₁	39,5 mm	Guidance rib diameter of inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0,36	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	1,67	Dynamic axial load factor
Y ₀	0,92	Static axial load factor

Additional information

T2CD025	Comparative designation to ISO 10317 and ISO 355
---------	--



Characteristics



Radial load



Axial load in one direction



Grease Lubrication



Oil Lubrication



Not sealed