


**FAG****33207-XL**

Tapered roller bearing

Tapered roller bearings 332, main dimensions
acc. to DIN 720, separable

X-life

Technical information



Your current product variant

Tolerance class	P6X	Class 6X (ISO 492:2023)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	Standard	
Quality level	XL	X-life
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	35 mm	Bore diameter
D	72 mm	Outside diameter
B	28 mm	Width, inner ring
C	22 mm	Width, outer ring
T	28 mm	Width, total
C _r	108.000 N	Basic dynamic load rating, radial
C _{0r}	105.000 N	Basic static load rating, radial
C _{ur}	17.100 N	Fatigue load limit, radial
n _G	12.300 1/min	Limiting speed
n _{gr}	6.200 1/min	Thermal speed rating
m	0,524 kg	Weight



Mounting dimensions

$d_{a \max}$	42 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	42 mm	Minimum diameter of shaft shoulder
$D_{a \min}$	61 mm	Minimum diameter of housing shoulder
$D_{a \max}$	65 mm	Maximum diameter of housing shoulder
$D_{b \min}$	68 mm	Minimum diameter of housing shoulder
$C_{a \min}$	5 mm	Minimum axial space
$C_{b \min}$	6 mm	Minimum axial space
$r_{a \max}$	1,5 mm	Maximum fillet radius of shaft
$r_{b \max}$	1,5 mm	Maximum fillet radius of housing

Dimensions

$r_{1, 2 \min}$	1,5 mm	Minimum chamfer dimension of inner ring back face
$r_{3, 4 \min}$	1,5 mm	Minimum chamfer dimension of outer ring back face
a	18 mm	Distance between the apexes of the pressure cones
d_1	53,9 mm	Guidance rib diameter of inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

e	0,35	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y	1,7	Dynamic axial load factor
Y_0	0,93	Static axial load factor

Additional information

T2DE035

Comparative designation to ISO 10317 and ISO 355



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed