

**FAG****32006-X-XL**

Tapered roller bearing

Tapered roller bearings 320, main dimensions
acc. to DIN 720, separable**X-life**

Technical information

Your current product variant

Tolerance class	P6X	Class 6X (ISO 492:2023)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Quality level	XL	X-life
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	30 mm	Bore diameter
D	55 mm	Outside diameter
B	17 mm	Width, inner ring
C	13 mm	Width, outer ring
T	17 mm	Width, total
C _r	48.000 N	Basic dynamic load rating, radial
C _{0r}	47.000 N	Basic static load rating, radial
C _{ur}	7.100 N	Fatigue load limit, radial
n _G	16.100 1/min	Limiting speed
n _{gr}	7.900 1/min	Thermal speed rating
≈m	180 g	Weight



Mounting dimensions

$d_{a \max}$	35 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	36 mm	Minimum diameter of shaft shoulder
$D_{a \min}$	48 mm	Minimum diameter of housing shoulder
$D_{a \max}$	49 mm	Maximum diameter of housing shoulder
$D_{b \min}$	52 mm	Minimum diameter of housing shoulder
$C_{a \min}$	3 mm	Minimum axial space
$C_{b \min}$	4 mm	Minimum axial space
$r_{a \max}$	1 mm	Maximum fillet radius of shaft
$r_{b \max}$	1 mm	Maximum fillet radius of housing

Dimensions

$r_{1, 2 \min}$	1 mm	Minimum chamfer dimension of inner ring back face
$r_{3, 4 \min}$	1 mm	Minimum chamfer dimension of outer ring back face
a	14 mm	Distance between the apexes of the pressure cones
d_1	43,9 mm	Guidance rib diameter of inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

e	0,43	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y	1,39	Dynamic axial load factor
Y_0	0,77	Static axial load factor

Additional information

T4CC030

Comparative designation to ISO 10317 and ISO 355



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed