



FAG

32026-X-XL

Tapered roller bearing

Tapered roller bearings 320, main dimensions
acc. to DIN 720, separable

X-life

Technical information



Your current product variant

Tolerance class	P6X	Class 6X (ISO 492:2023)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Quality level	XL	X-life
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	130 mm	Bore diameter
D	200 mm	Outside diameter
B	45 mm	Width, inner ring
C	34 mm	Width, outer ring
T	45 mm	Width, total
C _r	405.000 N	Basic dynamic load rating, radial
C _{0r}	550.000 N	Basic static load rating, radial
C _{ur}	81.000 N	Fatigue load limit, radial
n _G	4.000 1/min	Limiting speed
n _{gr}	2.320 1/min	Thermal speed rating
≈m	5,05 kg	Weight



Mounting dimensions

$d_{a \max}$	144 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	140 mm	Minimum diameter of shaft shoulder
$D_{a \min}$	178 mm	Minimum diameter of housing shoulder
$D_{a \max}$	190 mm	Maximum diameter of housing shoulder
$D_{b \min}$	192 mm	Minimum diameter of housing shoulder
$C_{a \min}$	8 mm	Minimum axial space
$C_{b \min}$	11 mm	Minimum axial space
$r_{a \max}$	2,5 mm	Maximum fillet radius of shaft
$r_{b \max}$	2 mm	Maximum fillet radius of housing

Dimensions

$r_{1, 2 \min}$	2,5 mm	Minimum chamfer dimension of inner ring back face
$r_{3, 4 \min}$	2 mm	Minimum chamfer dimension of outer ring back face
a	44 mm	Distance between the apexes of the pressure cones
d_1	165,9 mm	Guidance rib diameter of inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

e	0,43	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y	1,38	Dynamic axial load factor
Y_0	0,76	Static axial load factor

Additional information

T4EC130

Comparative designation to ISO 10317 and ISO 355



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed