



**FAG****22248-BE-XL-K**

Spherical Roller Bearing

Spherical roller bearings 222...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

X-life

Technical information



Your current product variant

Design	BE	With lose center lip ring
Bore type	K	Tapered, taper 1:12
Cage	JPB	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	240 mm	Bore diameter
D	440 mm	Outside diameter
B	120 mm	Width
C _r	2.230.000 N	Basic dynamic load rating, radial
C _{0r}	2.900.000 N	Basic static load rating, radial
C _{ur}	255.000 N	Fatigue load limit, radial
n _G	1.900 1/min	Limiting speed
n _{gr}	1.200 1/min	Reference speed
≈m	78 kg	Weight



Mounting dimensions

$d_{a \min}$	257 mm	Minimum diameter shaft shoulder
$d_{a \max}$	283 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	423 mm	Maximum diameter of housing shoulder
$r_{a \max}$	3 mm	Maximum recess radius
$d_{b \min}$	254 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	19 mm	Minimum cavity width of the sleeve

Dimensions

$r_{\min}$	4 mm	Minimum chamfer dimension
D_1	380,4 mm	Bore diameter outer ring
d_2	285,6 mm	Raceway diameter of the inner ring
d_s	12,5 mm	Diameter lubrication hole
n_s	23,5 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,26	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,55	Dynamic axial load factor
Y_2	3,8	Dynamic axial load factor
Y_0	2,5	Static axial load factor

Additional information

H3148X	Adapter sleeve
AH2248	Withdrawal sleeve



Characteristics



Radial load



Axial load in one direction



Axial load in two directions



Grease Lubrication



Oil Lubrication



Not sealed



Large bearing



Static angular error and misalignment



Dynamic angular error and misalignment