

**FAG****33020**

Tapered roller bearing

Tapered roller bearings 330, main dimensions
acc. to DIN 720, separable

Technical information



Your current product variant

Tolerance class	P6X	Class 6X (ISO 492:2023)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	Standard	
Quality level	Standard	
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	100 mm	Bore diameter
D	150 mm	Outside diameter
B	39 mm	Width, inner ring
C	32,5 mm	Width, outer ring
T	39 mm	Width, total
C_r	225.000 N	Basic dynamic load rating, radial
C_{0r}	395.000 N	Basic static load rating, radial
C_{ur}	48.500 N	Fatigue load limit, radial
n_G	4.450 1/min	Limiting speed
n_{gr}	2.900 1/min	Thermal speed rating
$\approx m$	2,411 kg	Weight



Mounting dimensions

d _a max	108 mm	Maximum diameter of shaft shoulder
d _b min	109 mm	Minimum diameter of shaft shoulder
D _a min	135 mm	Minimum diameter of housing shoulder
D _a max	141 mm	Maximum diameter of housing shoulder
D _b min	143 mm	Minimum diameter of housing shoulder
C _a min	7 mm	Minimum axial space
C _b min	6,5 mm	Minimum axial space
r _a max	2 mm	Maximum fillet radius of shaft
r _b max	1,5 mm	Maximum fillet radius of housing

Dimensions

r _{1, 2} min	2 mm	Minimum chamfer dimension of inner ring back face
r _{3, 4} min	1,5 mm	Minimum chamfer dimension of outer ring back face
a	29 mm	Distance between the apexes of the pressure cones
d ₁	124,7 mm	Guidance rib diameter of inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0,29	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	2,09	Dynamic axial load factor
Y ₀	1,15	Static axial load factor

Additional information

T2CE100	Comparative designation to ISO 10317 and ISO 355
---------	--



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed