



**FAG****24032-BE-XL**

Spherical Roller Bearing

Spherical roller bearing 240...-BE-XL,
symmetric with rib washer

X-life

Technical information



Your current product variant

Design	BE	With lose center lip ring
Bore type	Z	Cylindrical
Cage	JPB	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	160 mm	Bore diameter
D	240 mm	Outside diameter
B	80 mm	Width
C_r	770.000 N	Basic dynamic load rating, radial
C_{0r}	1.240.000 N	Basic static load rating, radial
C_{ur}	140.000 N	Fatigue load limit, radial
n_G	2.550 1/min	Limiting speed
n_{gr}	1.660 1/min	Reference speed
$\approx m$	12,67 kg	Weight

Mounting dimensions

$d_{a \min}$	170,2 mm	Minimum diameter shaft shoulder
$D_{a \max}$	229,8 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,1 mm	Maximum recess radius



Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
D_1	212,5 mm	Bore diameter outer ring
d_2	179,3 mm	Raceway diameter of the inner ring
d_s	4,8 mm	Diameter lubrication hole
n_s	9,5 mm	Width of lubricating groove

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

Calculation factors

e	0,29	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,32	Dynamic axial load factor
Y_2	3,45	Dynamic axial load factor
Y_0	2,26	Static axial load factor

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment