



FAG


24048-BE-XL

Spherical Roller Bearing

Spherical roller bearing 240...-BE-XL,
symmetric with rib washer

X-life

Technical information



Your current product variant

Design	BE	With lose center lip ring
Bore type	Z	Cylindrical
Cage	JPB	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	240 mm	Bore diameter
D	360 mm	Outside diameter
B	118 mm	Width
C_r	1.670.000 N	Basic dynamic load rating, radial
C_{0r}	2.850.000 N	Basic static load rating, radial
C_{ur}	280.000 N	Fatigue load limit, radial
n_G	1.710 1/min	Limiting speed
n_{gr}	980 1/min	Reference speed
$\approx m$	41,61 kg	Weight

Mounting dimensions

$d_{a \min}$	252,4 mm	Minimum diameter shaft shoulder
$D_{a \max}$	347,6 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,5 mm	Maximum recess radius



Dimensions

r_{min}	3 mm	Minimum chamfer dimension
D_1	317,2 mm	Bore diameter outer ring
d_2	268,5 mm	Raceway diameter of the inner ring
d_s	6,3 mm	Diameter lubrication hole
n_s	12,2 mm	Width of lubricating groove

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

Calculation factors

e	0,3	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,28	Dynamic axial load factor
Y_2	3,39	Dynamic axial load factor
Y_0	2,23	Static axial load factor

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Large bearing
-  Static angular error and misalignment
-  Dynamic angular error and misalignment